




R-Series Dia-Vac - R272 (50 Hz)



Max Pressure = 75.0 PSIG (5.17 barG) **Parallel**
75.0 PSIG (5.17 barG) **Series**
Max Vacuum = 25.3 InHg (856 mBarG) **Parallel**
Max Flow = 55.6 SLPM (1.97 SCFM) **Parallel**
29.0 SLPM (1.03 SCFM) **Series**

-Test results are averaged, and therefore should be considered approximate.
-These test results are for reference only, and are intended to help provide information to the user when determining which pump to buy. Actual pump performance will depend upon the users' applications.
-For 60 Hz operation, increase output by 20%.